




MATERIAL ABS-CF10 **OVERVIEW**



ABS-CF10

Carbon Fiber Filled ABS FDM Thermoplastic Filament





Overview

Stratasys ABS-CF10 combines standard ABS (acrylonitrile butadiene styrene) material with 10% chopped carbon fiber by weight. The result is a low moisture-sensitive FDM® thermoplastic 50% stiffer and 15% stronger than standard ABS 3D printing material.

Typical applications include manufacturing tools, jigs, fixtures and end effectors that benefit from the combination of increased stiffness and reduced weight.

Contents:

| Product and Ordering Information | 3 |
|--|---|
| Physical Properties | 4 |
| Mechanical Properties | 5 |
| Mechanical Performance with Unidirectional Toolpaths | 7 |
| UV Aging | 8 |
| Appendix | 9 |





Product Information

Table 1: Printer Compatibility

| Printer | Model Tip | Layer Height | Support Material | Support Tip |
|---------|----------------------------|---|------------------|-------------|
| F170™ | F123 T14H Hardened Head | 0.127 mm (0.005 in.), 0.178 mm (0.007 in.), 0.254 mm (0.010 in.), 0.330 mm (0.013 in.) | QSR™ Support | F123 Head |
| F190™CR | F123 T14H Hardened Head | 0.127 mm (0.005 in.), 0.178 mm (0.007 in.), 0.254 mm (0.010 in.), 0.330 mm (0.013 in.) | QSR Support | F123 Head |
| F370™ | F123 T14H Hardened Head | 0.127 mm (0.005 in.), 0.178 mm (0.007 in.), 0.254 mm (0.010 in.), 0.330 mm (0.013 in.) | QSR Support | F123 Head |
| F370®CR | F123 T14H Hardened Head | 0.127 mm (0.005 in.), 0.178 mm (0.007 in.), 0.254 mm (0.010 in.), 0.330 mm (0.013 in.) | QSR Support | F123 Head |

Support Material

· QSR soluble support

Build Tray

- F170 build tray
- F190CR build tray
- F370/F370CR build tray

System Requirements¹

F123/F123 CR²

F123 T14H hardened head (light gray cover, 1,500 hour head life)³

F123 ABS-CF10 non hardened head hardened head (green cover, 700 hour head life)

Standard F123 head (black cover, recommended head life of 700 hours)

Table 2: ABS-CF10 Ordering Information

| Part Number | Description | System Compatibility |
|----------------------|---|----------------------------|
| Filament Consumables | 3 | |
| F123 Spools | | |
| 333-90310 | ABS-CF10, 90 cu. in. | F170, F190CR, F370, F370CR |
| 333-63500 | QSR Soluble Support, 60 cu. in F123 | F170, F190CR, F370, F370CR |
| Printer Consumables | | |
| F123 | | |
| 123-00302-S | F170 Build Tray, Standard | F170 |
| 123-00303-S | F190CR Build Tray, Standard | F190CR |
| 123-00304 | F370/F370CR Build Tray, Standard | F370, F370CR |
| Print Heads | | |
| F123 | | |
| 123-00603-S | ABS-CF10 Hardened Head - Recommended (Light Gray Cover) | |
| 123-00601-S | ABS-CF10 Head (Green Cover) | F170, F190CR, F370, F370CR |
| 123-00402-S | Standard Extrusion Head (Black Cover) | |

¹ Contact your Stratasys representative for ordering information

²F170, F190CR, F370, F370CR

³ Required for Visual Mode; 0.127 mm (0.005 in.) layer height



Physical Properties

The information presented are typical values intended for reference and comparison purposes only. They should not be used for design specifications or quality control purposes.

Values are measured as printed. XY, XZ, and ZX orientations were tested. DSC and TMA curves can be found in the Appendix.

Table 3: ABS-CF10 Physical Properties


| Droporty | Test Method | Typical V | alues | | | |
|----------------------|-----------------------------------|----------------------------------|----------------------------------|--|--|--|
| Property | Test Method | XY | XZ/ZX | | | |
| HDT @ 66 psi | ASTM D648 Method B | 112.2 °C (234.0 °F) | 113.5 °C (236.4 °F) | | | |
| HDT @ 264 psi | ASTM D648 Method B | 111 A °C (222 6 °E) 112 | | | | |
| Molded HDT @ 66 psi | ASTM D648 Method B | 100 °C (21 | 100 °C (212 °F) | | | |
| Molded HDT @ 264 psi | ASTM D648 Method B | 99 °C (21 | 99 °C (210 °F) | | | |
| Tg | ASTM D7426 Inflection Point | 104 °C (21 | 104 °C (219 °F) | | | |
| Mean CTE | ASTM E831 (-50 °C to 100 °C) | 19 μm/[m*°C] (11 μin/[in*°F]) | 76 μm/[m*°C] (42 μin/[in*°F]) | | | |
| Volume Resistivity | ASTM D257 | 4.6 x 10 ¹² | 4.6 x 10 ¹² Ω*cm | | | |
| Specific Gravity | ASTM D792 @23 °C | 1.097 | 1.0972 | | | |
| Dielectric Constant | ASTM D150 1 kHz test condition | 2.26 | 11.1 | | | |
| Dielectric Constant | ASTM D150 2 MHz test condition | 2.16 | -0.001 | | | |
| Dissipation Factor | ASTM D150 1 kHz test condition | 0.000 | -0.011 | | | |
| Dissipation Factor | ASTM D150 2 MHz test condition | 10.18 | -0.014 | | | |



Mechanical Properties


ABS-CF10 samples were printed with a 0.254 mm (0.010 in.) layer height on the F370 using the Standard Extrusion Head.

Print Orientation Parts created using FDM are anisotropic as a result of the printing process. Below is a reference of the different orientations used to characterize the material.



Tensile Curves

Due to the anisotropic nature of FDM, tensile curves look different depending on orientation. Below is a guide of the two types of curves seen when printing tensile samples and what reported values mean.



- A = Tensile at break, elongation at break (no yield point)
- B = Tensile at yield, elongation at yield
- C = Tensile at break, elongation at break



Table 4: ABS-CF10 Mechanical Properties

| 0.010 in layer height | | XZ Orientation ¹ | ZX Orientation ¹ | | | | |
|--|-----------------|-----------------------------|-----------------------------|--|--|--|--|
| Tensile Properties: ASTM D638 | | | | | | | |
| Viold Ctrongth | MPa | No yield | 21.2 (0.48) | | | | |
| Yield Strength | psi | No yield | 3,080 (69) | | | | |
| Elongation @ Yield | % | No yield | 1.49 (0.08) | | | | |
| Strength @ Break | MPa | 37.7 (1.38) | 21.3 (0.48) | | | | |
| Strength (i) Break | psi | 5,465 (200) | 3,100 (70) | | | | |
| Elongation @ Break | % | 2.70 (0.20) | 1.49 (0.09) | | | | |
| Modulus (Elastic) | GPa | 3.342 (0.12) | 1.958 (0.028) | | | | |
| Wodulus (Elastic) | ksi | 484.6 (18) | 283.9 (4.1) | | | | |
| Flexural Properties: ASTM D7 | 90, Procedure A | | | | | | |
| Strength @ Break | MPa | 69.0 (2.4) | 29.2 (0.86) | | | | |
| Strength @ break | psi | 10,000 (350) | 4,240 (120) | | | | |
| Strain @ Break | % | 2.45 (0.11) | 1.89 (0.08) | | | | |
| Modulus | GPa | 3.76 (0.099) | 1.75 (0.051) | | | | |
| Wodulus | ksi | 545 (14) | 254 (7.5) | | | | |
| Compression Properties: AST | M D695 | | | | | | |
| Yield Strength | MPa | No yield | No yield | | | | |
| Heid Strength | psi | No yield | No yield | | | | |
| Peak Strength | MPa | 73.2 (4.5) | 94.8 (2.56) | | | | |
| Peak Strength | psi | 10,260 (650) | 13,740 (370) | | | | |
| Madulus | GPa | 2.129 (0.093) | 1.917 (0.063) | | | | |
| Modulus | ksi | 309 (13.6) | 278 (9.2) | | | | |
| Impact Properties: ASTM D256, ASTM D4812 | | | | | | | |
| Notched | J/m | 51.4 (1.9) | 20.3 (2.8) | | | | |
| Notched | ft*lb/in | 0.962 (0.04) | 0.381 (0.05) | | | | |
| Unnotched | J/m | 212 (25) | 47.0 (6.4) | | | | |
| offilotofied | ft*lb/in | 3.97 (0.47) | 0.881 (0.12) | | | | |

¹Values in parentheses are standard deviations.



Mechanical Performance with Unidirectional Toolpaths

ABS-CF10 samples were printed with a 0.254 mm (0.010 in.) layer height on the F370CR using the T14H Hardened Extrusion Head. The Stratasys typical testing procedure follows our default "45/-45" raster toolpath generation where the first raster layer is 45° in the XY plane and the next layer is perpendicular to that (-45°). The data in this section has unidirectional toolpaths, where all toolpaths are aligned in the XY plane and along the axis for the mechanical test. This method of optimizing toolpaths is appropriate to show the maximum strength for filled materials, but should be used with caution as it is not representative of typical part toolpaths and strength.

Table 5: Mechanical Performance of ABS-CF10 with Unidirectional Toolpaths

| 0.010 in layer height | | XY Orientation | | | | |
|--------------------------------------|--|----------------|--|--|--|--|
| Tensile Properties: ASTM D638 | | | | | | |
| Yield Strength | MPa | 44.9 | | | | |
| Held Stieligtii | psi | 6,500 | | | | |
| Elongation @ Yield | % | 1.2 | | | | |
| Strength @ Break | MPa | 44.6 | | | | |
| Stieligtii (@ bieak | psi | 6,470 | | | | |
| Elongation @ Break | % | 1.2 | | | | |
| Modulus (Elastic) | GPa | 5.22 | | | | |
| Modulus (Liastic) | ksi | 756 | | | | |
| Flexural Properties: ASTM D790, Prod | cedure A | | | | | |
| Strength @ Break | MPa | 89.3 | | | | |
| Strength (ii) break | psi | 31.0 | | | | |
| Strain @ Break | % | 2.6 | | | | |
| Modulus | GPa | 4.96 | | | | |
| Modulus | ksi | 719 | | | | |
| Impact Properties: ASTM D256, ASTM | И D4812 | | | | | |
| Notched | J/m | 79.2 | | | | |
| Notcheu | ft*lb/in | 1.48 | | | | |
| Heat Deflection Temperature: ASTM | Heat Deflection Temperature: ASTM D648, Method B | | | | | |
| HDT @ 66 psi | °C | 117 | | | | |
| 1151 @ 66 psi | °F | 242 | | | | |
| HDT @ 264 psi | °C | 112 | | | | |
| 1161 @ 201 psi | °F | 233 | | | | |



UV Aging

ABS-CF10 samples were printed with a 0.254 mm (0.010 in.) layer height on the F370 using the Standard Extrusion Head. ABS-CF10 was tested before and after UV exposure. Ten ASTM D638 upright (ZX) dogbones were tested in tensile after UV exposure and an additional 10 ASTM D638 ZX dogbones were the control (no UV Exposure). The UV exposed samples were cycled in the QUV chamber per ASTM G154 (Standard Practice for Operation Fluorescent Light Apparatus for UV exposure of Nonmetallic Materials) for 1,000 hours, alternating for 8 hours at 60°C (140°F) and 4 hours at 50°C (122°F) with humidity and condensation. The increase in stress in break is from the control samples.

Table 6: ABS-CF10 UV Exposure Test Results

| Material | Conditioning | Yield St | ld Strength Stress at Break | | Elongation at Break | Increase in Stress at Break | Modulus | | |
|----------|----------------|----------|-----------------------------|-------|------------------------|-----------------------------------|---------|-------|-------|
| | | (psi) | (MPa) | (psi) | (MPa) | % | % | (ksi) | (GPa) |
| ABS-CF10 | No UV Exposure | 3,150 | 21.7 | 3,140 | 21.7 | 1.5 | | 284 | 1.96 |
| | UV Exposure | 301 | 20.8 | 2,990 | 20.6 | 1.3 | -4.90 | 295 | 2.03 |



Appendix

Figure 1: DSC data for the ABS-CF10 sample.




Figure 2: Dimension change data as a function of temperature for ABS-CF10 Flat (XY) sample.







Figure 3: Dimension change data as a function of temperature for ABS-CF10 On Edge (XZ) sample.



Find the Perfect Material for Your Application

From strength and flexibility to biocompatibility and color, our experts help you select materials that meet your part performance and production goals - every time.

TALK TO AN EXPERT

Visit https://theD2Mco.com/contact-us





